



COMFORT THERMOMETER

Operating Instructions

Product code:
810-135

INSTRUMENT OPERATION - Open the battery compartment and insert the batteries supplied. For the most accurate recording of ambient temperatures, the Comfort thermometer should be positioned away from direct sunlight or draughts. The coloured indicators above the temperature and humidity display are a quick reference guide to temperature levels only.

MAX/MIN - Press the MAX/MIN button to display the maximum reading ('MAX' symbol displayed). Press the MAX/MIN button again to display the minimum reading ('MIN' symbol displayed). Press MAX/MIN button again to return to normal readings. To clear the MAX or MIN reading, press the clear button when viewing the MAX or MIN readings, '- -' will be shown and readings cleared.

Please note: Max/Min readings are not saved, so if the battery is removed or drained, the Max/Min readings will be cleared.

°C/°F - Press the °C/°F button on the front of the instrument to switch between Centigrade and Fahrenheit.

BATTERY REPLACEMENT - Replace the batteries when the display dims, using 2 x AAA or 1.5 volt equivalent. The batteries are located under the battery cover at the rear of the instrument.

GUARANTEE - This instrument carries a one-year guarantee against defects in either components or workmanship. During this period, products that prove to be defective will, at the discretion of ETI, be either repaired or replaced without charge. The product guarantee does not cover damage caused by fair wear and tear, abnormal storage conditions, incorrect use, accidental misuse, abuse, neglect, misapplication or modification. Full details of liability are available within ETI's Terms & Conditions of Sale at etiltd.com/terms. In line with our policy of continuous development, we reserve the right to amend our product specification without prior notice.

Specification

Range	0 to 50 °C or 10 to 99 %rh
Resolution	0.1 °C/°F or 1 %rh
Accuracy	±1 °C or ±5 %rh 30 %rh - 70 %rh @25 °C
Battery	2 x 1.5 volt AAA
Battery life	10000 hours
Display	Dual custom LCD
Dimensions	20 x 100 x 110 mm
Weight	150 grams



PROMAT (HK) LIMITED 寶時儀器 (香港) 有限公司
Tel: +852 2661 2392 | Fax: +852 2661 2086

810-135/28.09.18